



MaxLiner Resin Saturation Chart

Recommended Resin Saturation Rates for MaxLiner® Liners:
 MaxPox® Resin with MaxPox 30, 60 or 180 Hardener

	2 mm	3 mm	4.5 mm	
MAX FlexLiner				
4"	-	0.75	1.00	
5"	-	0.85	1.30	
6"	-	0.90	1.50	
MAX LinerTube Reinforced - SCRIM				
3"	-	0.56	-	
4"	-	0.75	1.00	
5"	-	0.93	1.30	
6"	-	1.10	1.50	
8"	-	1.50	2.00	
10"	-	1.65	2.50	
MAX SuperFlex				
2"	0.25	-	-	
3"	0.35	-	(T) 0.80	(D) 0.90
4"	0.45	-	(T) 1.00	(D) 1.25
5"	-	-	(T) 1.30	(D) 1.50
6"	-	-	(T) 1.50	(D) 1.75
8"	-	-	(T) 2.00	(D) 2.50
10"	-	-	(T) 2.50	(D) 3.00
MAX WovoLiner				
2"	0.25	-	-	
3"	0.35	-	0.70	
4"	0.45	-	0.80	
5"	-	-	1.00	
6"	-	-	1.20	
8"	-	-	1.60	
MaxLiner Flex 4D				
4"	-	-	1.10	

Call our technical advisor with additional questions at 877.426.5948

Disclaimer: The information contained herein is offered without charge for use by technically qualified personnel at their discretion and risk. All statements, technical information and recommendations contained herein are based on test and data which we believe to be reliable, but the accuracy or completeness thereof is not guaranteed and no warranty of any kind is made with respect thereto. Always read, understand, and comply with hazard warnings described in the products' Safety Data Sheet(s) before use.